

AMF-Bruns Platinum Restraints

Your vehicle is fitted with AMF-Bruns Platinum Series Restraints for restraining wheelchairs of up to 160kg. Platinum Series retractors should be used to restrain the rear of the wheelchair.

Please note, although visually similar, Platinum Series retractors are larger in size than Silver Series and have “Platinum Heavy Duty” embossed on the underside. They also have “Platinum Series” on the tag attached to the webbing part of the restraint.

SILVERSERIES



PLATINUMSERIES HEAVY DUTY HD160



Important Safety Notes

Always take care to ensure the wheelchair is correctly restrained.

Always take care to ensure the wheelchair occupant is correctly restrained. Please read the Restraint Guidance in your WAV Owner's Handbook for further important information to ensure the safe transportation of the wheelchair and occupant.

If you have any questions about your vehicle, please do not hesitate to call us on **01924 442386** or email customerservices@bristolstreetversa.com